



HIGH-SPEED, NON-GLASS COMPACT DR

The HPX-DR 2530 PC Non-Glass detector is designed specifically for customer's looking for reliable, high-speed NDT imaging in a compact and durable DR package.

The HPX-DR 2530 PC has a 145 μm resolution and a lower required exposure dose to achieve faster throughput for imaging, which in turn accelerates the process of analysis and reporting.

The non-glass detector design incorporates a tougher material instead of glass which virtually eliminates costly repairs for broken glass. With its compact size, the new HPX-DR 2530 PC is ideal for imaging applications in confined areas or in between objects.

All Carestream NDT CR and DR products run on our all-in-one INDUSTREX software, so you don't need to purchase costly add-on modules to utilize the benefits of both.

BENEFITS AT A GLANCE

- 145 μm resolution for precision imaging and detailed analysis
- Less required dose for shorter exposure times and faster throughput
- Compact size (250 x 300mm) and thin profile (14.7mm) for positioning in tight spaces
- Tungsten shielding for higher cumulative dose while preserving image quality
- Protective, weatherproof enclosure for use in harsh environments
- Close-to-edge imaging maximizes surface area for image capture
- Robust wireless connectivity for faster image transfer and analysis
- Lithium-ion batteries with battery 'hot-swap' to keep the detector running during battery change



COMES WITH A 2-YEAR WARRANTY AND FREE LOANER PROGRAM!

We're so confident in the design and reliability of this detector that we're offering a two-year warranty. If your detector ever does need service, we offer a loaner service (US and Canada only) to minimize downtime and avoid the expense of purchasing a back-up detector.